

CC-106A

Clear View Circulator Bath consisting of transparent baths made of polycarbonate with temperature range up to max. 100°C. Powerful pressure and suction pump made of industrial plastic material. With adjustable overtemperature protection according to DIN 12876.

Pilot ONE:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 11 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

The range of functions can be expanded very easily via E-grade at any time by entering a unit specific upgrade code:

E-grade "Exclusive": TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 3 programs (max. 15 steps), ramp function (linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K.

E-grade "Professional": Programmer with 10 programs (max. 100 steps), ramp function for temperature gradients (linear and non-linear), 2nd set point, user menus (Administrator level), calendar start.

3-2-1 warranty - registration required.

Technical data according to DIN 12876

from Serial-No :	1/0355	1 0/1
max. ambient temperature	40 °C	
min. ambient temperature	5 °C	
Degree of Protection	IP20	
max. Fuse (1 phase)	16A	
min. Fuse (1 phase)	10A	
alternative max. current	10 A	
alternative power supply	240V 1~ 60Hz	
max. current	10 A	
Power supply requirement	230V 1~ 50/60Hz	Order-No.: 2001.0001.01
Net weight	5 kg	
Overall dimensions WxDxH **	147x307x330 mm	W.
Width bath opening WxD/ bath depth	130x110/ 150 mm	
Filling capacity	4,9	1064
Bath volume	6	huber
Pump connenction (optional)	M16x1 male	
max. delivery pressure (suction)	0,4 bar	
max. delivery (suction)	25 l/min	
Suction pump	yes	
max. delivery pressure	0.7 bar	
max. delivery	27 l/min	
Pressure pump		
Heating power	2 kW	
Safety classification	Class III / FL	huber
	Device), RS232	
Interface digital	Ethernet, USB (Host u.	ELAL INVESTIGATION
Sensor external connection	Pt100	
Internal temperature sensor	Pt100	
Absolute accuracy	setup for calibration	- 79.99 ·
temperature set point / display	5,7" colour Touchscreen	Piabar
Temperature stability at 70°C	0,02 K	
with refrigerator	15100 °C	
with water cooling	20100 °C	
Operating temperature range	25100 °C	
Operating temperature range	25 100 °C	

from Serial-No.:

149355

1.0/12

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions.

Technical data according to DIN 12876

Accessories and periphery: mini-USB cable #54949*, Bath cover #37533, Bath Bridges #19592, Cooling coil #30554, pump adaptor #19606, Note: When using Huber pump adapter: Polyglycol is not permissible to be used as a heat transfer fluid,polycarbonate test tube racks Typ A-F, nozzle #33288, DS level regulator #9580 * standard equipment

Output data valid for: Room temperature 20°C In accordance with EN60034-1 the following voltage and frequency tolerances are valid: Voltage + / - 10%, as long as the frequency tolerance does not run in the opposite direction. Example: -10% voltage and + 3% frequency -> not allowed ! -10% voltage and -3% frequency -> allowed.

Information to Electromagnetic compatibility: Classification (disturbance) to EN55011: Class B, Group 1

** Please respect space requirements. See operating conditions at www.huber-online.com