

Grande Fleur



Hydraulically sealed Refrigerated Heating Circulator with air-cooled refrigerating unit. With atmospheric open expansion tank and optical level indicator. For externally closed applications. Powerful, variable speed pump, housing of stainless steel, CFC and H-CFC free. With adjustable overtemperature protection according to DIN 12876. High system performance (watt/litre) due to minimized internal volume. No HTF vapour and no moisture absorption because the expansion tank is thermally passive.

Pilot ONE:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 11 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

further functions:

E-grade Professional installed as standard, TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 10 programs (max. 100 steps), ramp function (linear and non-linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K, integrated technical glossary, 2nd set point, user menus (Administrator level), calendar start, wallpaper selection.

3-2-1 warranty - registration required.

Technical data according to DIN 12876

Operating temperature range Temperature stability at -10°C temperature set point / display

Resolution of display Internal temperature sensor Sensor external connection

Interface digital

digital input digital output Alarm message Safety classification Heating power Cooling power with

at 200°C at 150°C at 100°C at 50°C at 20°C

Cooling power with

at 0°C at -20°C at -30°C at -40°C

Refrigeration machine

Refrigerant

Refrigerant quantity Gas warning sensor Circulation pump: max. delivery

max. delivery pressure Pump connection

max. permissible kin. viscosity

min. filling capacity

Filling capacity expansion tank

Overall dimensions WxDxH **

-40...200 °C 0.01 K

- -"

5,7" colour Touchscreen

0,01 K Pt100 Pt100

Ethernet, USB (Host u. Device), RS232

ECS ONE POKO ONE

optic, acoustic, relay

Class III / FL 1,5 kW Thermooil 0,6 kW 0,6 kW 0,6 kW 0,6 kW 0,6 kW Ethanol 0,6 kW

0,35 kW 0,2 kW 0,04 kW

air-cooled, natural refrigerant

R290 0,1 kg without

3 I

38 l/min 0.9 bar M24x1,5 male 50 mm²/s 1.5 l

295x540x565 mm



Order-No.: 1041.0001.01

Technical data according to DIN 12876

from Serial-No.:	196251	1.0/14
max. ambient temperature	40 °C	
min. ambient temperature	5 °C	
min. Fuse (1 phase) max. Fuse (1 phase) Degree of Protection	10A 16A IP20	
max. current	9,5 A	
Power supply requirement	230V 1~ 50Hz	
Net weight	55 kg	

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions.

Accessories and periphery: mini-USB cable #54949*, E-grade "Professional" #9496*, E-grade "Explore" #10495, Adaptor M16x1 male to M24x1,5 female*, SpyLight-Software, Com.G@te, Thermofluid, metal hoses M16x1 or M24x1,5, external pressure sensor

Note: Pump connections: Bore shape Y (60°) according to DIN 3863, pipework/flexible tempering hoses: Ball socket according to DIN 3863, sleeve nut according to DIN 3870.

Output data valid for: Room temperature 20°C

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

Example -5% voltage and +2% frequency -> not allowed! -5% voltage and -2% frequency -> allowed

Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class B, Group 1

Peter Huber Kältemaschinenbau GmbH Werner-von-Siemens-Str. 1 D-77656 Offenburg Tel 0781/9603-0 Fax 0781/57211 www.huber-online.com

^{*} standard equipment

^{**} Please respect space requirements. See operating conditions at www.huber-online.com